




50/15 PRIME E

Cod. PR-OF200-040-AN

Oil free compressors, FAD at 8 bar 110 l/min, tank capacity 40 L, internally coated against corrosion, complete with the new adsorption air dryer able to deliver -40°C dew point value. The compressor has a maximum pressure of 10 bar. Compressed air quality in conformity with the ISO 8573-1 (class 2-1-1) and the European Pharmacopeia in matter of medical air.

Air Dryer	Air capacity		FAD @ 8bar		Motor	Voltage Hz	Receiver	Noise Level	Duty Cycle	max P.	Size	net Weight
Yes	m³/min	l/min	m³/min	l/min	kW	230V 50Hz	l	db(A)	100 %	bar	mm	Kg
	0.24	240	0.11	110	1.5		40	66		10	740x410x770	47

Air delivery performance



Maintenance kits

Kit.	Description	Type	Hours
------	-------------	------	-------

TA-FL-026-K-SCP	<p>PRIME 2-3 M filter cartridges kit</p> <p>Cartridge replacement kit for ordinary maintenance of the PURE AIR PRIME 2.3 M range.</p> <p>Comprehends:</p> <ul style="list-style-type: none"> • 3 suction filters, code: TA-FL-058-C • 1 5 micron filter cartridge, code: TA-FL-001-C-SM • 1 0.01 micron filter cartridge, code: TA-FL-024-C2-SM • 2 o-rings for filters, cod. TA-FL-001-OR • 1 non-return valve pads, code: CO-PV-001 • 1 5 micron filter cartridge (AF30), code: TA-FL-075-C • 1 0.01 micron filter cartridge (AFD30), code: TA-FL-076-C • 2 o-rings for filters, cod. TA-FL-075-OR • 1 AMG150 water separator filter cartridge, code: TA-FL-074-C <p>Replace the filtration cartridges every 2 years.</p>	Ordinary	1.500h/2y
PR-GC-032-K-SCP	<p>PRIME 3</p> <p>Extraordinary maintenance spare parts kit for PRIME 2.2 kW (PRIME 3) versions.</p> <p>comprehends:</p> <ul style="list-style-type: none"> • 3 suction filters, code: TA-FL-058-C • 6 O-rings, code: MA-PC018 • 3 piston rings , code: MA-MG00001 • 3 piston guide rings, code: MA-MG00003 • 3 expansion rings for the segments, code: MA-MG00024 • 3 complete valve plates, code: MA-MG-02002P-C-P • 1 non-return valve pads, code: CO-PV-001 <p>The recommended maintenance intervals for this compressor are 4000 hours/4 years.</p>	Extraordinary	4.000h/4y